


HONEYWELL  
PART NUMBER

4

| REV | DOCUMENT | CHANGED BY  | CHECK |
|-----|----------|-------------|-------|
| A   | 0016306  | LKM 24OCT05 | VA    |

B

B



| ELECTRICAL RATINGS AND APPROVALS |        |       |
|----------------------------------|--------|-------|
| 10A                              | 250VAC | 1/2HP |
| 15A                              | 125VAC | 1/2HP |
| UL, CSA                          |        |       |

|     |    |   |   |   |   |   |
|-----|----|---|---|---|---|---|
| SRN | XX | - | X | X | X | X |
|     | 91 |   | 1 | 1 | B | B |
|     |    |   | 2 | 2 | G | G |
|     |    |   | 3 | 3 | R | W |
|     |    |   | 4 | 4 | W |   |
|     |    |   | 5 |   |   |   |
|     |    |   | 6 |   |   |   |
|     |    |   | 7 |   |   |   |
|     |    |   | 8 |   |   |   |

| CIRCUIT MADE WITH ROCKER IN 5 |                          |            |                          |
|-------------------------------|--------------------------|------------|--------------------------|
|                               | POSITION 3<br>(1&2, 4&5) | POSITION 2 | POSITION 1<br>(2&3, 5&6) |
| 1                             | ON                       | OFF        | ON                       |
| 2                             | OFF                      | NONE       | ON                       |
| 3                             | ON                       | NONE       | ON                       |
| 4                             | (OFF)                    | NONE       | ON                       |
| 5                             | (ON)                     | OFF        | ON                       |
| 6                             | OFF                      | NONE       | (ON)                     |
| 7                             | (ON)                     | OFF        | (ON)                     |
| 8                             | (ON)                     | NONE       | ON                       |

- 1 - OPERATING TEMPERATURE RANGE : -40°F TO +185°F (-40°C TO +85°C)
- 2 - ELECTRICAL LIFE : 50,000 CYCLES MOMENTARY, 100,000 CYCLES MAINTAINED
- 3 - MECHANICAL LIFE : 150,000 CYCLES MIN
- 4 - SEE DIAGRAM FOR CATALOGING SCHEME
- 5 - PARENTHESIS DENOTE MOMENTARY ACTION
- 6 - SEALED TO IP68

|                                                                                                                                                                                                    |                                                                                                                                                           |     |           |                                     |           |                                    |  |              |          |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|-----|-----------|-------------------------------------|-----------|------------------------------------|--|--------------|----------|
| DESIGN UNITS: INCH<br>TOLERANCES UNLESS NOTED:<br><br>NO PLACE X ± 0.040<br>ONE PLACE .X ± 0.030<br>TWO PLACE .XX ± 0.015<br>THREE PLACE .XXX ± 0.015<br>FOUR PLACE .XXXX ± 0.0005<br>ANGLES X ± 2 | DRAWN                                                                                                                                                     | TSG | 15 JUL 05 | <div>Honeywell</div>                |           |                                    |  |              |          |
|                                                                                                                                                                                                    | CHECK                                                                                                                                                     | -   | -         |                                     |           |                                    |  |              |          |
|                                                                                                                                                                                                    | THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL.<br>THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL. |     |           | TITLE<br><div>SWITCH , ROCKER</div> |           |                                    |  |              |          |
|                                                                                                                                                                                                    | INTERPRET PER ASME Y14.5M-1994<br>OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY                                                                         |     |           | SIZE<br>B                           | TYPE<br>I | DRAWING NAME<br>SRN SERIES CHART 1 |  |              | REV<br>A |
|                                                                                                                                                                                                    | THIRD ANGLE PROJECTION<br>                                           |     |           | Pro/ENGINEER 2D                     |           | SCALE -                            |  | SHEET 1 OF 1 |          |

A

A