

RoHS

MATERIAL&FINISH

Insulator: PBT Glass Fiber(UL94V-0)

Contact Material: Terminal Brass.

Shell Spcc.

Contact Plating : Terminal Gold-Plated Over Nickel.

Shell Nickel OR TIN.

SPECIFICATIONS

Current Rating :1A AC, DC

Voltage Rating : 250V AC, DC






Temperature Range: -40 ° C To+105 ° C

Contact Resistance : 20M Ω Max

Insulation Resistance :1000M Ω Min

Withstanding Voltage:500V AC/Min

REV.	DESCRIPTION	DATE
A		2016.04.12
B	Add Dim. 'F'	2019.03.18
C	Dim. 'F' Tolerance Change	2019.08.12




NUMBER OF POSITIONS	DIMENSION					
	A	B	C	D	E	F
9	30.80	25.00	16.95	11.08	10.16	11.68
15	39.14	33.30	25.3	19.39	17.78	19.30
25	53.05	47.04	38.96	33.24	30.48	32.00
37	69.32	63.50	55.42	49.86	45.72	47.24

CnC Tech, LLC

Part NO.

410M0-XX-1-00

UNLESS TOLERANCE		DRAW BY			
GENERAL	ANGLE	DESIGN BY	CHECK BY	APPROVE BY	SCALE
X. ± 0.38 .X ± 0.30 .XX ± 0.25 .XXX ± 0.10	X.° ± 3.0° .X.° ± 2.0° .XX.° ± 1.0° .XXX ± 0.5°				1:1
					1/1
					MM



SCALE

SHEET

UNIT

DRW NO:

REV: C

Downloaded from Arrow.com