


OA172SAPL Series



AC Fans - 115, 230V
172mm x 150mm x 38mm
(6.7" x 5.9" x 1.5")



Frame	Die Cast Aluminum, Black Finish	<u>Operating Temperature</u> -40°C ~ +70°C	
Impeller	PBT, UL94 V-0 Plastic	<u>Storage Temperature</u> -40°C ~ +80°C	
Connection	2x Wire Leads, or Terminals	<u>Life Expectancy</u> 40,000 Hours (L10 at 40°C)	
Motor	AC, Capacitor Induction, Thermally Protected, Class B Insulation	<u>Available Options</u> Tachometer Output Alarm Output	
Bearing System	Ball Bearings	Weight: 1.7 lbs	
Dielectric Strength	500VAC/min, <5mA		
Insulation Resistance	≥10MΩ @ 500VDC		

Part Number	Rated Voltage (Volts AC)	Voltage Range (Volts AC)	Input Power (Watts)	Frequency (Hertz)	Rated Speed (RPM)	Max Airflow (CFM)	Noise Level (dBA)	Max Static Pressure (\"H2O)
OA172SAPL-11-1*B	115	80 ~ 125	29 / 28	50 / 60	2800 / 3400	175 / 211	54 / 58	0.67 / 0.75
OA172SAPL-11-2*B	115	80 ~ 125	29 / 28	50 / 60	2300 / 2750	133 / 160	47 / 50	0.33 / 0.35
OA172SAPL-11-3*B	115	80 ~ 125	29 / 28	50 / 60	1400 / 1700	84 / 102	35 / 38	0.17 / 0.25
OA172SAPL-22-1*B	230	220 ~ 240	27 / 28	50 / 60	2800 / 3400	175 / 211	54 / 58	0.67 / 0.75

* Substitute "T" for terminal type power connection, or "W" for lead wire type power connection.
-60Hz values shown in PQ diagram.