



Part Number : [2138652333](#)

Product Description : NTC Ring Temperature
Sensor-to-Micro-Lock Plus Cable Assembly, 75.00mm
Length, 3982 Beta Value with 1% Tolerance, 3kOhm
Resistance at 25°C with 2% Tolerance

Series Number : 213865

Status : Active

Product Category : Power and Signal Cable
Assemblies



Documents and Resources

Drawings

[2138652333 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 15(a) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	213865
Description	NTC Ring Temperature Sensor-to-Micro-Lock Plus Cable Assembly, 75.00mm Length, 3982 Beta Value with 1% Tolerance, 3kOhm Resistance at 25°C with 2% Tolerance
Application	Temperature Sensing
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Ring Term-to-Micro-Lock Plus
Product Name	NTC Temperature Sensor
Type	Discrete Wire Assembly
UPC	193264438495

Electrical

Beta Value (K)	3982
Current - Maximum per Contact	0.5A
Resistance at 25°C (kohms)	3
Resistance Tolerance (%)	2
Voltage - Maximum	50V AC (RMS)/DC

Physical

Cable Length	75.00mm
Circuits (Loaded)	2

Circuits (maximum)	2
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel, Tin
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	1.732/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Single Ended	No
Stud Size	6 (M3.5)
Termination Interface Style	Crimp or Compression
Wire/Cable Type	PTFE, UL 10344
Wire Size (AWG)	26

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.25mm Pitch Micro-Lock Plus Vertical, Single Row, Surface Mount Headers	<u>505568</u>
1.25mm Pitch Micro-Lock Plus Right-Angle, Single Row, Surface Mount Headers	<u>505567</u>

This document was generated on Apr 21, 2026