

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301020215

Status:

Active

Overview:

Hand Lamps

Description:

Super-Safeway Rubber Hand Lamp, Nylon Quick Open Guard, with Switch

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E59251

General

Product Family

Series

NEMA Configuration

Outlet

Overview

Product Name

Taxonomy

Type

UPC

Portable Lighting

130102

N/A

None

Hand Lamps

Super-Safeway

Lamps and Lights

Hand Lamps

78678860588

Physical

Cord Length - Primary

Cord Length - Secondary

Depth

Duty

Guard Included

Guard Type

Height

Length

Material - Guard

Mounting Style

Packaging Type

Socket Construction

N/A

N/A

127.00mm (5.000")

Industrial

Yes

Quick Open

400.05mm (15.750")

N/A

Nylon

Hand Held

Carton

N/A

Electrical

Bulb Type

Cord Type - Primary

Lamp Type

Lamp Wattage - Maximum

Lumens

On/Off Switch

Voltage (Fixture) - Maximum

Incandescent

16/3 SOOW

A21

100W

1000

Yes

240V

Material Info

Engineering Number

118S



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130102 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION