

# Product data sheet

Specifications



## APC IT Power Distribution Module 3 Pole 4 Wire 50A CS50 380cm

PDM3450CS50-380

### Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

### General

Provided equipment	Installation guide
--------------------	--------------------

### Physical

Colour	Black
Depth	40.6 cm
Height	12.7 cm
Net weight	4.27 kg
Width	44.5 cm

### Input

Network frequency	60 Hz
Permissible voltage	200...240 V
Max line current	50 A
Input voltage	208 V 3 phases

### Output

Max current draw	50 A
Number of power socket outlets	1 CS50
Output connector type	CS50 1
Output voltage	208 V 3 phases

### Conformance

Product certifications	UL listed
------------------------	-----------

### Packing Units

Package 1 Weight	4.82 kg
------------------	---------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	12.7 cm
Package 1 width	44.5 cm
Package 1 Length	40.6 cm

Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------