



Data Sheet | Item Number: 286-664

Current flow monitoring module; AC currents; Monitoring range: 0.2 A – 3 A; 1 changeover contact; light gray

<https://www.wago.com/286-664>



Color:  light gray



Technical data

Input

Voltage drop	44 ... 430 mV
Response time	300 ms

Power supply

Current consumption at nominal supply voltage	≤ 17 mA
---	---------

Signaling

Status indicator	Red LED; Energized relay (current < switching threshold)
------------------	--

Safety and protection

Rated Voltage	250 V
Rated impulse withstand voltage	4 kV
Pollution degree	2
Dielectric strength, input/output (AC, 1 min)	1.5 kVrms



Physical data	
Width	25 mm / 0.984 inches
Height	52 mm / 2.047 inches
Depth from upper-edge of DIN-rail	82.5 mm / 3.25 inches

Mechanical data	
Mounting type	Pluggable module for receptacle terminal blocks
Housing design	Plug for carrier terminal blocks

Material data	
Color	light gray
Fire load	9.713 MJ
Weight	58 g

Environmental requirements	
Ambient temperature (operation)	-25 ... +40 °C
Ambient temperature (storage)	-40 ... +70 °C
Relative humidity	5 ... 95 % (no condensation permissible)
Operating altitude (max.)	2000 m

Commercial data	
Product Group	6 (INTERFACE ELECTRONIC)
PU (SPU)	10 (1) pcs
Packaging type	Box
Country of origin	DE
Customs tariff number	85364900990

Product classification	
UNSPSC	39122331
eCl@ss 10.0	27-37-18-02
eCl@ss 9.0	27-37-18-02
ETIM 9.0	EC001440
ETIM 8.0	EC001440
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
CAS-No.	1303-86-2 1317-36-8 7439-92-1 79-94-7
REACH Candidate List Substance	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol Diboron trioxide Lead Lead monoxide
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	34 6(c) 7(a) 7(c)-I 7(c)-II
SCIP notification number (Bulgaria)	98f1e7db-5d3f-4985-ba66-d049a4d62a4c
SCIP notification number (Czech Republic)	626b9169-c297-4aa1-a143-52c79b974e50



Main product function		Current flow monitoring module
Product type		Specialty electronics
Series		286

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 286-664	

Documentation

Bid Text			
286-664	19.02.2019	xml 3.74 KB	
286-664	02.04.2015	doc 25.00 KB	

Instruction Leaflet			
Operation and Assembly Instructions Interface	V 1.0.0 02.04.2025	pdf 1246.19 KB	

CAD/CAE-Data

CAD data	
2D/3D Models 286-664	

CAE data	
WSCAD Universe 286-664	
ZUKEN Portal 286-664	



1 Compatible Products
1.1 Optional Accessories
1.1.1 Marking
1.1.1.1 Marker



Item No.: 209-701
WSB marking card; as card; not stretchable; plain; snap-on type; white

1.1.2 Terminal blocks
1.1.2.1 Terminal block for pluggable modules



Item No.: 280-639
Terminal block for pluggable modules; 10-pole; with 2-conductor terminal blocks; with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray



Item No.: 280-765
Terminal block for pluggable modules; 10-pole; with 4-conductor terminal blocks; with marker carrier; with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray



Item No.: 280-629
Terminal block for pluggable modules; 10-pole; with 4-conductor terminal blocks; with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray