

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0685324510

Status:

Active

Overview:

In-Vehicle Smart Charging Modules

Description:

In-Vehicle Single Port USB Smart Charger with Backlight, 2.4A



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Datasheet (PDF)	

General	
Product Family	I/O Connectors
Series	72610
Application	Module-to-Wire
Component Type	USB Charger
Overview	In-Vehicle Smart Charging Modules
Product Name	Mini50, USB
Taxonomy	I/O Connectors
Type	A
UPC	191128281102
Physical	
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	10000
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	ABS, PC
Net Weight	29.659/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	2.4A
Voltage - Maximum	16V DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	685324510-000

EU ELV

Compliant with Exemption 8(e),10(a)

EU RoHS

Compliant with Exemption 7(a),7(c)-I,6(c)

China RoHS

REACH SVHC

Not Contained Per - ECHA_01_2020 (16 January 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Compliant with Exemption 8(e),10(a)

RoHS Phthalates

Not Contained

Search Parts in this Series

72610 Series

Mates With

USB Type A (Front)
Mini50 Unsealed Receptacle [347910040](#) (Rear)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION