

Downloaded from Arrow.com.

REVISION			
LTR	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09-14-04	LE

SPECIFICATIONS

1. CASE:
   22 GA. (.030) CRS, TIN PLATED
2. RATED CURRENT:
   50A
3. RATED VOLTAGE:
   250VAC, 50/60Hz
4. TEST VOLTAGE:
   LINE TO LINE: 1.7KVDC
   LINE TO GROUND: 2.2KVDC
5. LEAKAGE CURRENT:
   1.4mA @ 250VAC, 50Hz






INSERTION LOSS (50Ω TYPICAL)

	.05 MHz	.15 MHz	.50 MHz	1.5 MHz	5.0 MHz	20 MHz
L/L	7 db	15 db	50 db	60 db	55 db	50 db
L/G	7 db	15 db	50 db	65 db	65 db	55 db

SCHEMATIC



NEXT ASSY	USED ON
APPLICATION	

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE INCHES
TOLERANCES ARE:
FRACTIONS ± DECIMALS .XX ±.030 .XXX ±.010 ANGLES ±

MATERIAL

FINISH

CONTRACT NO.

APPROVALS	DATE
DRAWN GIANG TRINH	10-03-02
CHECKED DANNIEL VUONG	09-14-04

FILTER CONCEPTS INC.

APPLICATION DRAWING
SE50 F FILTER

SIZE	CODE IDENT NO.	DRAWING NO.
B		7634

SCALE 2/3 SHEET 1 OF 1

GCT/1998