SLC40AB-0804A Product Details



SLC40AB-0804A

Braid, Fixed, Spin and Tinel Lock Adapters

Not EU RoHS or ELV Compliant

Product Highlights:

- Applies To Cable
- Style = Raychem Spinlock Variable Angle Backshells
- Connector Code = 40
- 45°, 90°, Straight
- Shell Size = 08

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

TE Internal Number: CX5689-000

Active

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information

Product Drawings:
- Spin-Lock Adapter Saddle Clamp, Code 40 (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Style = Raychem Spinlock Variable Angle Backshells
- Angle = 45°, 90°, Straight
- Shell Size = 08
- Finish = Cadimium over Nickel
- Material = Aluminum

Electrical Characteristics:
- Entry Diameter (mm [in]) = 6.40 [0.250]
- Manufacturer = Raychem
- Finish Code = B
- Tinel-Lock Ring Supplied = TR04AI

Body Features:
- Connector Code = 40
- Entry Size = 4
- Cable Diameter (Max.) (mm [in]) = 2.49 – 5.94 [0.098 – 0.234]

Configuration Features:
- Material Code = A

Industry Standards:
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:
- Applies To = Cable

Other:
- Brand = Raychem

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved | Privacy Policy

Provide Website Feedback

Downloaded from Arrow.com.