



Part Number : [1300060643](#)

Product Description : Mini-Change A-Size Single-Ended Cordset, 3 Poles, Male (90°) to Pigtail, 16 AWG, PVC Cable, 0.91m (3.0') Length

Series Number : 130006

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 103003A01F030

Documents and Resources

Drawings

[1300060643_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 3 Poles, Male (90°) to Pigtail, 16 AWG, PVC Cable, 0.91m (3.0') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	N/A
Type	Single Ended
UPC	78678843236

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Physical

Cable Diameter	10.41mm (.410")
Cable Length	0.91m (3.0')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC

Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	175.160/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	STOOW
Wire Size (AWG)	16

This document was generated on Dec 26, 2025