



+ RELAYS, CONTACTORS & SWITCHES
HIGH VOLTAGE RELAYS



✓ Active

TE CONNECTIVITY (TE)
LEV200ALANA= RELAY 110VDC SPST-NO
Kilovac

LEV200ALANA
TE Internal Number: 2-1618389-9

- EU RoHS Compliant
- EU ELV Compliant
- Contact Arrangement 1 Form X, SPST-NO-DM
- Contact Current Rating (A) 500
- Coil Voltage Rating (VDC) 110
- Mounting Type Bottom

↓ 3D PDF

DOCUMENTATION

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

5-1773450-5_sec7_LEV200

PDF

English

Agency Approvals

UL

CONTACTOR, MODELS EV200, LEV200, LEV100 AND EVC135 REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Product Type Contactor

Electrical Characteristics

Coil Voltage Rating (VDC) 110

Contact Features

Contact Arrangement 1 Form X, SPST-NO-DM

Contact Current Rating (A) 500

Mechanical Attachment

Mounting Type Bottom

Statement of Compliance

Statement of Compliance

PDF