



Part Number : [1301360055](#)

Product Description : Super-Safeway Multi-Tap (3)
Non-NEMA 20A/125V/250V Outlet Box with Buss Bars,
7.62m (25.0') Cord Length, 14/3 SOW Cord, Non-NEMA
20A/125V/250V Plug

Series Number : 130136

Status : Obsolete

Product Category : Power Distribution

Engineering Number : 32708A143



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Power Distribution
Series	130136
Description	Super-Safeway Multi-Tap (3) Non-NEMA 20A/125V/250V Outlet Box with Buss Bars, 7.62m (25.0') Cord Length, 14/3 SOW Cord, Non-NEMA 20A/125V/250V Plug
Enclosure Rating	N/A
NEMA Configuration	Non-NEMA
Product Name	Super-Safeway
Type	Multi-Tap and Strip Cordset
UPC	78678875659

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	120V

Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	Double C-Clamp
Cord Length	7.62m (25.0')
Cord Type	14/3 SOOW
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Mounting Style	Portable

Number of Receptacles	3
Packaging Type	Carton
Receptacle Type	Triple

This document was generated on Sep 13, 2025

Obsolete