

Isobar 2-Outlet Surge Protector, Direct Plug-In, 1410 Joules, Diagnostic LEDs, Black Metal Housing

MODEL NUMBER: ULTRABLOK



Premium protection for A/V home theater components and computer peripherals against dangerous power surges, spikes and line noise.

Description

Premium protection for your expensive computer and audio/visual equipment, the ULTRABLOK Isobar® 2-Outlet Surge Protector features a surge protection rating of 1410 joules to defend your sensitive electronics against even the strongest surges and spikes.

The ULTRABLOK features two NEMA 5-15R outlets, perfect for your flat-panel HDTV and Blu-ray player or a pair of computer peripherals, such as a printer and a router. This unique protection system prevents disruptive line noise from causing A/V distortion, computer lock-ups, data errors and similar problems. Large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors remove EMI/RFI interference and prevent system crashes, reboots and performance problems. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the ULTRABLOK protects all three, covering two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

An integrated 15A circuit breaker protects all outlets and shuts down connected equipment in the event of an overload. Diagnostic LEDs show power, protection and line fault status at a glance. The ULTRABLOK plugs directly into any standard NEMA 5-15R outlet. Optional mounting hardware is included for permanent attachment to the outlet cover, which will prevent the ULTRABLOK from coming loose accidentally.

Features

1410-Joule Surge Protection for Your Home Theater and Office Electronics Protects your components against surges and spikes
Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
2 NEMA 5-15R surge-protected outlets
Exceeds IEEE 587 Category A and B surge suppression specifications

Premium Safety Features Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
Diagnostic LEDs confirm power, protection and ground status at a glance
Conforms to current UL 1449 3rd Edition safety standards

Fits Effortlessly Into Your Setup Plugs directly into standard NEMA 5-15R outlet with no power cord
Optional hardware included for permanent mounting to outlet cover
Metal housing designed for long life

Backed by Ultimate Lifetime Insurance \$10,000 Ultimate Lifetime Insurance covers any connected

Highlights

- 2 NEMA 5-15R surge-protected outlets
- 1410-joule surge protection rating
- Durable metal housing mounts out of sight behind furniture
- 15A resettable circuit breaker prevents dangerous overloads
- Plugs directly into outlet with no power cord

Package Includes

- ULTRABLOK Isobar 2-Outlet Surge Protector, Black Metal Housing
- Mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

components damaged by power surge (U.S., Canada and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332010476
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	15
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1410
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	48,000 amps
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes and VHF capacitors
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended overvoltages and catastrophic occurrences
EMI / RFI Filtering	40-80 dB



Powering Business Worldwide

TRIPP LITE
SERIES

Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Metal
Form Factors Supported	Direct plug-in format with retaining bracket supports wall mounting directly to a standard AC wall socket
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	5.40 x 2.60 x 3.90
Shipping Dimensions (hwd / cm)	13.72 x 6.60 x 9.91
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
Unit Dimensions (hwd / in.)	4.000 x 2.500 x 2.500
Unit Dimensions (hwd / cm)	10.16 x 6.35 x 6.35
Unit Weight (lbs.)	.8
Unit Weight (kg)	0.36
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Mounting Accessory Included	Yes
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico); UL 1449; UL 1363
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.