53POS, MIXED,REC HSG,ASSY,SEALED









✔ ACTIVE

MQS

TE Part # **8-2208801-4**
TE Internal #: **8-2208801-4**
All MQS, CONNECTOR HOUSING (585)

Connector Style : **Housing for female terminals**
Mating Tab Width (mm): **.63, 1.5, 2.8**
Mating Tab Width (in): **.025, .059, .11**
Connector System : **Wire-to-Board, Wire-to-Device**
Number of Positions : **53**
Sealable : **Yes**

Add to List

ORDER SAMPLES

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America

Request pricing, availability and customization options

CONTACT US

We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

DOCUMENTS | FEATURES | PRODUCT COMPLIANCE

Product Drawings	53POS, MIXED,REC HSG,ASSY,SEALED 53POS, MIXED,REC HSG,ASSY,SEALED English
CAD Files	3D PDF 3D_CVM_CVM_8-2208801-4_B.pdf 3D Customer View Model ENG_CVM_CVM_8-2208801-4_B.2d_dxf.zip English ENG_CVM_CVM_8-2208801-4_B.3d_igs.zip English ENG_CVM_CVM_8-2208801-4_B.3d_stp.zip English
Catalog Pages/Data Sheets	ENG_CS_1307999-3_Micro_Quadlok__1211_1307999-3.pdf English

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Downloaded from Arrow.com.

Product Type Features	Connector Style : **Housing for female terminals** Connector System : **Wire-to-Board, Wire-to-Device** Sealable : **Yes** Hybrid Connector : **Yes** Primary Locking Feature : **Integrated in Housing** Strain Relief : **Yes**
Configuration Features	Number of Positions : **53** Number of Rows : **5**
Electrical Characteristics	Operating Voltage (VAC): **14**
Body Features	Color : **Black** Cable Exit Angle : **Other** Body Material : **PA GF**
Contact Features	Mating Tab Width (mm): **.63, 1.5, 2.8** Mating Tab Width (in): **.025, .059, .11**
Mechanical Attachment	Mounting Feature : **Without** Polarized : **No**
Dimensions	Length : **44 mm [1.732 in]** Width : **45.8 mm [1.803 in]** Height : **65 mm [2.559 in]**
Usage Conditions	Operating Temperature Range : **-40 – 125 °C [-40 – 257 °F]**
Operation/Application	Circuit Application : **Signal**
Other	Connector Position Assurance Capable : **No** Serviceable : **Yes**
Statement of Compliance	Statement of Compliance pdf

Downloaded from Arrow.com.

Compatible Parts



TE Part # 1326032-2
2.8MM RECP, SEAL, 20AWG

View Product



TE Part # 1326032-3
2.8MM RECP, SEAL, 18AWG

View Product



TE Part # 1326032-5
2.8MM RECP, SEAL, 14AWG

View Product



TE Part # 638652-1
RECEPT, 1.5MM, TIN 14-16AWG RD=1

View Product


Also in the Series | MQS



Automotive Connector Caps & Covers (138)



Automotive Connector EMC Shielding (2)



Automotive Connector Locks & Position Assurance (27)



Automotive Seals & Cavity Plugs (34)

Customers Also Bought



TE Part # 280543-5
FF 250 REC HSG 2P NYLON BLACK

Downloaded from Arrow.com.

© 2018 TE Connectivity. All Rights Reserved.

Downloaded from Arrow.com.