

Part Number : [1301510013](#)

Product Description : Super-Safeway Adapter
NEMA 5-15R Receptacle - Female End 15A/125V, Non-
NEMA Plug - Male End, 15A/125V

Series Number : 130151

Status : Active

Product Category : Wiring Devices


Engineering Part Number : 1704



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130151
Description	Super-Safeway Adapter NEMA 5-15R Receptacle - Female End 15A/125V, Non-NEMA Plug - Male End, 15A/125V
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Specialty	N/A
Type	Adapter
UPC	78678875005

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	50.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Male
Length	N/A
Lighted Connector	No
Locking Blade	No
Net Weight	79.832/g
Poles	2-pole/3-wire

Receptacle Type	N/A
-----------------	-----

This document was generated on Jan 01, 2026