



Pushing Performance
Since 1945

ICC20_H_BS_ST_M32_f.400A



Image is for illustration purposes only. Please refer to product description.

Part number	19 59 120 4015
Specification	ICC20_H_BS_ST_M32_f.400A
HARTING eCatalogue	https://harting.com/19591204015

Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Backshell
Description of hood/housing	with integrated M32 thread Straight

Version

Size	20
Number of cable entries	1
Cable entry	1x M32
Details	for exclusive use with the ICC Size 20 400 A insert

Technical characteristics

Tightening torque	15 Nm Backshell
Limiting temperature	-40 ... +125 °C
Number of relockings	≥10
Degree of protection acc. to IEC 60529	IP67 IPX9

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61984
	IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Net weight	80 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140491106
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405