

Catalog No. TYH28M

Description: CABLE TIE 50LB 14IN GR NYL HEAT STB

UPC No 786210811000

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Heat Stabilized Polyamide (Nylon 6.6) - Greenish Tint for Temperatures up to 105 Degrees Celsius (221 F) for Indoor Applications, Length of 360mm (14.2 Inches), Width of 4.2mm (0.19 Inch), Thickness of 1.3mm (0.05 Inch), Maximum Bundle Diameter 102mm (4.02 Inches), Tensile Strength Rating of 220 Newtons (49 Pounds)

Representative Image

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Green Tint
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds , 534 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

Dimensions

Width	0.19 in , 4.2 mm
Length	14.2 in , 360 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	Max 4.02 in , Max 102 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	4.2 mm
Length belt/tape/tie	360 mm
Length belt/tape/tie	14.17 inch

by ABB

ETIM	EC000046 Cable tie
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	102 mm
Min. holding force	534 N
Operation temperature	-40-+105 °C
Operation temperature	-40-+221 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Surface protection	Untreated
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y
Inflammability class of insulation material acc. with UL94	V0