



**Part Number :** [2001220008](#)  
**Product Description :** Mega-Fit Receptacle Backshell, Dual Row, Low-Halogen, 8 Circuits  
**Series Number :** 200122  
**Status :** Active  
**Product Category :** Connector Accessories  
**Engineering Number :** F4068.04-P27



Documents & Resources

Drawings

[2001220008\\_sd.pdf](#)

3D Models and Design Files

[2001220008\\_stp.zip](#)

Specifications

[AS-76823-100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Connector Accessories
Series	200122
Description	Mega-Fit Receptacle Backshell, Dual Row, Low-Halogen, 8 Circuits
Component Type	Backshell
Product Name	Mega-Fit
UPC	889056290975

#### Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.060/g
Number of Rows	2
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

#### Use with Part(s)

Description	Part Number
-------------	-------------

Mega-Fit Dual Row Receptacle Housings	<u>171692</u>
--	---------------

This document was generated on Apr 22, 2025