

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=VL40515000J0G* > VL40515000J0G

VL40515000J0G

VL40515000J0G - Terminal Blocks : Pluggable socket (male header), 5.08mm pitch, vertical, 2-row , 40 position



ACTIVE

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Customer drawing

Environmental Compliance Report

Specifications

Download document

General	Dimensional	Electrical	Mechanical	Physical	Approvals / Certifications	Mounting
General						
Gender	Socket (male header)					
Orientation	Vertical					
Packaging	Box					
Product Type	Pluggable Socket					
Series	VL					
Number of Positions	40					
Dimensional						
Pitch	5.08 mm					
Electrical						
Withstanding Voltage	1.6 kV					
Current rating	20 A					
Voltage rating	300 V					
Mechanical						
Number of mating cycles	200					
Physical						
Soldering temperature (celcius)	260 +/- 5 Celcius (5 sec)					
Color (Housing)	Green					
Material (Housing)	Thermoplastic UL94V-0					
Terminal material	Copper					
Terminal plating	Tin					
Temperature (Operating - range)	-40 to +115 Celcius					
Approvals / Certifications						
Approvals / Certifications	cULus					
Mounting						
Board attachment	TMT					

Disclaimer : The information above is for reference only. For more technical details , refer to product specification and application specification.

Downloaded from [Arrow.com](https://arrow.com).