



Dieless Mechanical Crimper, Heavy Duty Forged Steel, #8 Str - 4/0 Str Copper Aircraft Cable

By Burndy
Catalog # [MY28](#)

Dieless Mech #8 Str- 4/0 Str CU Aircraft

Features

- Easy to adjust nest die with knurled steel knob and machine heads
- Rugged tool design with heavy duty forged steel with reinforced back and handles
- Bench mount adapter (sold separately) available
- 31" diameter hole for bench mounting operations

Application

Crimping

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	EX
Buy America(n) Qualified	Contact Manufacturer

Conductor

Crimping Ranges	#8 Str. - 4/0 Str.
-----------------	--------------------

Dimensions

Length	22.65 in
--------	----------



Width	4.86 in
Weight	8 lb.
Height	1.12 in
Dimensions	22.65 in x 4.86 in x 1.12 in

General

Sub Brand	HYTOOL
Trade Name	HYTOOL™
Application - For Use On	#8-4/0 AWG Copper Aircraft Cable (YAV-L, YSV-L)
UPC 12 Digit	781810461952
UPC 14 Digit GTIN	00781810461952
Finish Type	Black Matte
Tool Type	Mechanical Dieless Crimper
UPC	781810461952
Die Type	Dieless

Logistics

Package Contents	Tool only
Minimum Pack Quantity	1

Product Assets

[Catalog \[English\]](#)