




- NOTES:
1. ALL PARTS TO BE BULK PACKED.
 2. CONTACTS ASSEMBLED INTO CONNECTOR.
 3. BACK WELL FILLED WITH EPOXY.
 4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.
 5. PC TAIL LENGTH OPTIONS:
 - STANDARD (SHORT) TAIL = 0.114in [W4281-1XPG-3ES]
 - INTERMEDIATE = 0.202in [W4291-1XPG-3ES]
 - LONG = 0.257in [W4292-1XPG-3ES]





FACE VIEW
W4281-10PG-3ES
10-POS.





FACE VIEW
W4281-11PG-3ES
11-POS.





FACE VIEW
W4281-12PG-3ES
12-POS.



PC TAIL LAYOUT



**RECOMMENDED
PANEL CUTOUT**
STANDARD MULTI-CON-X



PC TAIL VIEW
W4281-10PG-3ES - 10-POS. (11&12 CLOSED)
W4281-11PG-3ES - 11-POS. (12 CLOSED)
W4281-12PG-3ES - 12-POS. (ALL OPEN)

ASS'Y P/N	CONTACTS	HOLE POS. CLOSED
W4281-10PG-3ES	10 - #20	11, 12
W4281-11PG-3ES	11 - #20	12
W4281-12PG-3ES	12 - #20	NONE
W4281-1XPG-3ES		

NO. OF CONTACTS

CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY:	_____
DATE:	_____

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1
REV.	INIT.	DATE	DESCRIPTION
	PAK	10/02/14	ORIG. DRAWN BY: DATE: 10/02/14
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			conxall 601 E. WILDWOOD VILLA PARK, IL 60181
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			
APPROVED BY:			TITLE: PANEL PIN, W/ EPOXY 12-POS., #20 PC TAIL, SHORT (STD.) MULTI-CON-X, E-KEY, WEATHER RESISTANT STANDARD PRODUCT
SCALE: NTS SIZE: B SHEET: 1 OF 1			CUSTOMER: STANDARD PRODUCT
FILE: W4281-1XPG-3ES DIRECTORY: SLW			PART NUMBER: W4281-1XPG-3ES
			REV A