Part Number : 2196712114
Product Description : Pre-Crimped Lead Mini-Fit Sigma/TPA2 Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Red
Series Number : 219671
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2196712114_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	219671
Description	Pre-Crimped Lead Mini-Fit Sigma/ TPA2 Female-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Red
Application	Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Sigma/TPA2-to-Pigtail
Product Name	Mini-Fit Sigma,Mini-Fit TPA2
UPC	195842811218

Electrical

Current - Maximum per Contact	11.5A
Voltage - Maximum	600V AC/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.896/g
Number of Rows	1
Packaging Type	Bag

Downloaded from Arrow.com.

Plating min - Mating	2.500µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	18

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Receptacle Housings	172708
Mini-Fit TPA2 and Mini-Fit Sigma Single Row Receptacle Housings	200453

Downloaded from Arrow.com.