

Product image  
not available

Representative Image

**Catalog No. NC25/RD/50M****Description: 25MM SOLID PA6 CONDUIT 50M - RD****UPC No 5020963050404****Home > Cable Protection Systems > Harnessflex > Flexible Non-Metallic Conduit**

Standard Weight, General Purpose Conduit, NC Size 25/NW Size 22, Outside Diameter 25.6mm, Inside Diameter 21.3mm, Static Bend Radius 40mm, High Flexibility and Fatigue Life, IP40 Rating, Polyamide 6, Reel Length 50 Meters, Red

**Descriptors**

Category	Flexible Non-Metallic Conduit
Application	Extensively Used in Harnesses on HGV and off Road Vehicles Applications Where Superior Protection Against Impact and Mechanical Shock is Preferred. The Conduit is Used for Both Chassis and Engine Applications and Can Be Used in a Wide Range of Temperatures

**Specifications**

Radius	Static: 40 mm
Flexibility	Very High
Material	Polyamide/Nylon 6
Color	Red

**Classifications**

Brand Name	Harnessflex
Standard	ADR Approved, RoHS, Conforms with End of Life Vehicle Directive (ELV)EU200/53/EC

**Dimensions**

Trade Size	NC25/NW22
Outside Diameter	25.6 mm
Inside Diameter	21.3 mm
Length	50 m

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

  
**by ABB**

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	25 mm
Nominal size in inch	3/4 inch
Outer diameter	25.6 mm
Inner diameter	21.3 mm
Material	Polyamide 6
Degree of protection (IP)	IP40
Fire resistance in accordance with UL94	HB
Bending radius, static	40 mm
UV resistant	Y
Colour	Red
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	N
Halogen free	Y