



+ RELAYS, CONTACTORS & SWITCHES
PUSHBUTTON SWITCHES



✓ Active

TE CONNECTIVITY (TE)
AV22 SPM 5A NO LED
[Alcoswitch](#) | [Alcoswitch AV](#)

AV2210000Q04
TE Internal Number: 2213771-1

- [EU RoHS Compliant](#)
- [EU ELV Compliant](#)
- Configuration (Pole-Throw)** Single Pole - Single Throw
- Number of Actuators** Single
- Actuator Profile** Flush
- Bushing Style** Threaded
- Illuminated** No

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

ANTI-VANDAL SWITCH 22mm NO LED
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Catalog Pages/Data Sheets

ALCOSWITCH Anti-Vandal Switch Flyer
PDF
English

Agency Approvals
UL Report

Anti Vandal Switches
PDF
English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features

Illuminated No
Actuator Style Round
Product Type Switch
Switch Type Pushbutton
Dust Proof Yes

Configuration Features

Configuration (Pole-Throw) Single Pole - Single Throw
Number of Actuators Single
Snap Action Without
Support Bracket Without
Tactile No
Operating Function Momentary
ESD Grounding Terminal Without
Detent Style Audible

Electrical Characteristics

Voltage Rating (VAC) 250

Body Features

Actuator Profile Flush
Bushing Style Threaded
Case Material PBT

Contact Features

Contact Current Rating (A) 5
Contact Plating Silver

Termination Features

Termination Type Wire Lugs

Mechanical Attachment

Mounting Type Panel
Mounting Angle Vertical

Housing Features

Process Sealed Yes

Dimensions

Bushing Length (in) 22

Statement of Compliance

Statement of Compliance
PDF