



Actual



Representative

Catalog Number: 2523
Product ID: 7TBD105240R0006
UPC Number: 78621002523
EAN Number: 05414363101611
Status: A

Liquidtight Strain Relief Cord Connector, 1/2 Inch, Straight, Cord Range 0.450 to 0.560 Inch, Die Cast Zinc

- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	1/2 Inch
Conductor Range	0.450 to 0.560 Inch
Material	Zinc Die Cast
Color	Metallic
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.875mm
Suitable for cable diameter	11.43-14.22mm
Material	Metal
Material quality	Other
Surface protection	Other
Degree of protection (IP)	Other
Colour	Natural colour
Model	Straight
Strain relief	Y
Type of sealing	Straight
Operating temperature	0-+105°C
For Ex-zone gas	Straight
For Ex-Zone dust	Straight

Packaging

Inner Quantity	25
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	100
Outer Dimensions (inches)	11x9.8x4.2
Weight Uom	14 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000046
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com