



4.8

18 Reviews



4.8

18 Reviews

Need Help?

[Browse All Products](#)[Cat5e / Cat6 / Cat6a](#)[Cat6](#)[Cat6 Patch Cable Value Packs](#)

Loading...

## 5ft Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable Multipack (50 pack) - Blue

Multi-Pack. Snagless design for network adapters, hubs, switches, routers, DSL/cable modems, patch panels and other high performance networking applications.



4.8

18 Reviews

97 In Stock & ready to ship! [\(i\)](#)

Add



### Need It shipped today?

Place your order before the timer runs out!


[print](#) [share](#) [chat](#)

Product # : 31372

Connector 1 : (1) RJ-45 Male

Connector 2 : (1) RJ-45 Male

Lengths : [5ft](#) [3ft](#) [7ft](#) [10ft](#) [14ft](#) [25ft](#)Packs : [50pk](#) [Single](#) [25pk](#)[Product Info](#)[Customer Reviews](#)[Questions & Answers](#)[Distributors](#)[More Choices](#)[Description](#)[Features](#)[Certifications](#)[Specs](#)[Uses](#)[Support](#)

### Product Description

For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

### Product Features

- Snagless design protects clips when plugging and unplugging
- Standard RJ45 connectors and unshielded twisted pair wires
- Available in 10 colors to color-code a network
- Available in lengths up to 150ft

**WARNING:** Cancer and Reproductive Harm [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

### Product Certifications



## Product Specifications

<b>Color :</b>	Blue
<b>Length :</b>	5.00 Foot
<b>Jacket Rating :</b>	Standard Non-Rated
<b>UPC :</b>	757120313724
<b>Warranty :</b>	Lifetime
<b>Vendor :</b>	C2G
<b>Weight :</b>	7.580 LB

### Electrical Characteristics

- Conductor DC Resistance - 9.38Ω/100m (maximum)
- Impedance - 100Ω
- Capacitance - 5600pf/100m
- Propagation Delay - 545ns/100m (maximum)
- Delay Skew - 45ns/100m (maximum)

### Physical Characteristics

- Wiring Scheme - T568B
- Standard: Category 6 TIA/EIA-568-B-2.1, draft 9
- Connector: 50 micron gold-plated RJ45
- Temperature Rating - 60°C
- Voltage Rating - 30V
- Approvals - RoHS Compliant
- Warranty - Lifetime
- Package Type - Polybag

#### **Conductor (Qty. 4 twisted pair)**

- Conductor Type - 24AWG (7/0.20), Stranded Bare Copper
- Insulation - H-D PE
- Diameter - 0.98 ± 0.05mm
- Colors - Blue, Blue-White, Orange, Orange-White, Green, Green-White, Brown, Brown-White

#### **Connector Type (Qty. 2)**

- Connector Type - 8P8C (RJ45)
- Gender - Male
- Connector Material - Polycarbonate
- Contact Material - Copper Alloy, Gold Plating - 50µm
- Hood Material - Molded PVC

#### **Overall Cable**

- Jacket - PVC
- Minimum Average Thickness - 0.60mm
- Outer Diameter - 6.20 ± 0.30mm

### Product Uses

- Gigabit 1000 BASE-T; 100 BASE-T; 10 BASE-T (IEEE 802.3)
- 4/16 Mbps Token Ring (IEEE 802.5); 100 VG-AnyLAN
- 100 Mbps TP-PMD (ANSI X3T9.5) 55/155 Mbps ATM

- Voice: T1

## Product Support

### Downloads

- Download the [technical specifications](#)

#### Info

- About Us
- Order History
- Where To Buy
- More ▾

#### Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

#### Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

#### Have A Question?

Get help with [Chat](#)  
Call C2G **800.506.9607**



[United States](#) | [Europe +](#)

Copyright © 2019 C2G. All Rights Reserved

