
**Part Number :** 151370502
**Product Description :** Mini-Lock-to-Mini-Lock Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Female-Female, Single Row, 150.00mm Length, 5 Circuits, Natural
**Series Number :** 15137
**Status :** Active
**Product Category :** Power and Signal Cable Assemblies



## Documents and Resources

### Drawings

151370502_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 15137 |
| Description | Mini-Lock-to-Mini-Lock Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Female-Female, Single Row, 150.00mm Length, 5 Circuits, Natural |
| Application | Wire-to-Board |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Mini-Lock-to-Mini-Lock |
| Product Name | Mini-Lock |
| Type | Discrete Wire Assembly |
| UPC | 191128925440 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 3.5A |
| Voltage - Maximum | 250V AC (RMS)/DC |

### Physical

| | |
|---|---|
| Cable Length | 150.00mm |
| Circuits (Loaded) | 5 |
| Circuits (maximum) | 5 |

Downloaded from Arrow.com.

| | |
|---|---|
| Color - Resin | Natural |
| Gender | Female-Female |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Matte Tin |
| Material - Plating Termination | Matte Tin |
| Material - Resin | Polyester |
| Net Weight | 6.380/g |
| Number of Rows | 1 |
| Overmolded | No |
| Packaging Type | Bag |
| Pitch - Mating Interface | 2.50mm |
| Plating min - Mating | 0.889µm |
| Single Ended | No |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 1061 |
| Wire Size (AWG) | 22 |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Mini-Lock Vertical Single Row Headers | 53375 |
| Mini-Lock Right-Angle Single Row Headers | 53426 |
| Mini-Lock Vertical Single Row Headers | 53517 |



Downloaded from Arrow.com.