



Technical Tapes

HelaTape Tex - Textile Tape

Features and Benefits

- High quality PE-coated cloth tape with good weather resistance
- Total thickness of 0.31 mm for high tensile strength
- Highly tear-resistant in longitudinal direction
- Easy to tear-off by hand in transverse direction
- Matt surface finish for use in stage constructions and for exhibitions to avoid light reflections
- Useful for various applications like bundling, fixing, identification, marking and protection
- HelaTape Tex can be removed without residues due to high quality rubber based adhesive



HelaTape Tex is available in various colours and sizes.

MATERIAL	Cotton (CO)
Adhesion to Backing	3 N/10 mm
Breaking Strength	64 N/10 mm
Elongation at break	10 %
Operating Temperature	-30 °C to +80 °C



TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-TEX-12x50	0.31	12.0	50.0 m	Black (BK)	712-00304
	0.31	12.0	50.0 m	Blue (BU)	712-00300
	0.31	12.0	50.0 m	Green (GN)	712-00303
	0.31	12.0	50.0 m	Grey (GY)	712-00306
	0.31	12.0	50.0 m	Red (RD)	712-00301
	0.31	12.0	50.0 m	White (WH)	712-00305
	0.31	12.0	50.0 m	Yellow (YE)	712-00302
HTAPE-TEX-15x25	0.31	15.0	25.0 m	Black (BK)	712-00054
	0.31	15.0	25.0 m	Blue (BU)	712-00050
	0.31	15.0	25.0 m	Green (GN)	712-00053
	0.31	15.0	25.0 m	Grey (GY)	712-00056
	0.31	15.0	25.0 m	Red (RD)	712-00051
	0.31	15.0	25.0 m	White (WH)	712-00055
	0.31	15.0	25.0 m	Yellow (YE)	712-00052
HTAPE-TEX-15x50	0.31	15.0	50.0 m	Black (BK)	712-00404
	0.31	15.0	50.0 m	Blue (BU)	712-00400
	0.31	15.0	50.0 m	Green (GN)	712-00403
	0.31	15.0	50.0 m	Grey (GY)	712-00406
	0.31	15.0	50.0 m	Red (RD)	712-00401
	0.31	15.0	50.0 m	White (WH)	712-00405
	0.31	15.0	50.0 m	Yellow (YE)	712-00402

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



Technical Tapes

HelaTape Tex - Textile Tape

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-TEX-19x25	0.31	19.0	25.0 m	Black (BK)	712-00154
	0.31	19.0	25.0 m	Blue (BU)	712-00150
	0.31	19.0	25.0 m	Green (GN)	712-00153
	0.31	19.0	25.0 m	Grey (GY)	712-00156
	0.31	19.0	25.0 m	Red (RD)	712-00151
	0.31	19.0	25.0 m	White (WH)	712-00155
	0.31	19.0	25.0 m	Yellow (YE)	712-00152
HTAPE-TEX-19x50	0.31	19.0	50.0 m	Black (BK)	712-00504
	0.31	19.0	50.0 m	Blue (BU)	712-00500
	0.31	19.0	50.0 m	Green (GN)	712-00503
	0.31	19.0	50.0 m	Grey (GY)	712-00506
	0.31	19.0	50.0 m	Red (RD)	712-00501
	0.31	19.0	50.0 m	White (WH)	712-00505
	0.31	19.0	50.0 m	Yellow (YE)	712-00502
HTAPE-TEX-25x25	0.31	25.0	25.0 m	Black (BK)	712-00254
	0.31	25.0	25.0 m	Blue (BU)	712-00250
	0.31	25.0	25.0 m	Green (GN)	712-00253
	0.31	25.0	25.0 m	Grey (GY)	712-00256
	0.31	25.0	25.0 m	Red (RD)	712-00251
	0.31	25.0	25.0 m	White (WH)	712-00255
	0.31	25.0	25.0 m	Yellow (YE)	712-00252
HTAPE-TEX-25x50	0.31	25.0	50.0 m	Black (BK)	712-00604
	0.31	25.0	50.0 m	Blue (BU)	712-00600
	0.31	25.0	50.0 m	Green (GN)	712-00603
	0.31	25.0	50.0 m	Grey (GY)	712-00606
	0.31	25.0	50.0 m	Red (RD)	712-00601
	0.31	25.0	50.0 m	White (WH)	712-00605
	0.31	25.0	50.0 m	Yellow (YE)	712-00602
HTAPE-TEX-50x25	0.31	50.0	25.0 m	Black (BK)	712-00354
	0.31	50.0	25.0 m	Blue (BU)	712-00350
	0.31	50.0	25.0 m	Green (GN)	712-00353
	0.31	50.0	25.0 m	Grey (GY)	712-00356
	0.31	50.0	25.0 m	Red (RD)	712-00351
	0.31	50.0	25.0 m	White (WH)	712-00355
	0.31	50.0	25.0 m	Yellow (YE)	712-00352
HTAPE-TEX-50x50	0.31	50.0	50.0 m	Black (BK)	712-00904
	0.31	50.0	50.0 m	Blue (BU)	712-00900
	0.31	50.0	50.0 m	Green (GN)	712-00903
	0.31	50.0	50.0 m	Grey (GY)	712-00906
	0.31	50.0	50.0 m	Red (RD)	712-00901
	0.31	50.0	50.0 m	White (WH)	712-00905
	0.31	50.0	50.0 m	Yellow (YE)	712-00902

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.