



C2G
Discontinued - 32.8ft (10m) MTP® Compatible MPO to MPO Fiber Array Cable Type B OM3 Riser Rated (OFNR)
Part No. 31311



This riser rated OM3 laser-optimized multimode (LOMMF) MPO fiber array cable is ready for deployment in any multimode 50/125 MTP/MPO network. OM3 is fully backward-compatible with existing OM2 or OM1 systems. This multimode, MPO fiber cable is comprised of 12 fiber channels within each connector. This high density MPO fiber cable is pinned out in type B format and is comprised of 12 fiber channels within each connector which is perfect when space is limited and makes it possible to run a single cable that automatically terminates 12 fibers in one easy plug-in. The push-pull release mechanism for the MPO connector is easy to engage and disengage, its latch design also prevents the plug from snagging when jumper cables are being routed.

Features & Benefits

Type B pinout	No guide pins on either MPO connector
The MPO connector has a push pull spring loaded release	Riser rated (OFNR) Jacket
3mm jacket outer diameter	

Specifications

General Info

Product Line	C2G	Color	Aqua
UPC Number	757120313113	Country Of Origin	Hong Kong
Type	Cable		

Dimensions

Cable Length	33 ft
--------------	-------

Technical Information

Fiber Optic Cable Type	MPO, MTP, Multimode, OM3	Jacket Material	PVC (Polyvinyl Chloride)
Jacket Application	Riser Rated	Jacket Rating	FT4 Rated, OFNR Rated
Cable Diameter	3 mm		