



Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings
 - DXF-Cable Manage ..
 - DWG-Cable Manage ..
 - PDF-Cable Manage ..
- Specification Sheets
 - PDF-PatchRunner ..
 - PDF-Cisco 2 Post ..
 - PDF-2 Post and 4 ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Standard Rac

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 


 Text Search: 'R2P79'

Your search criteria matched only one product, shown below

R2P79



- Rack space identification allows quick and easy location of rack mount items
- 3" Rack is UL listed for 1,000 lbs. load rating
- 6" Rack is UL listed for 1,500 lbs. load rating
- Double-sided #12-24 EIA universal mounting hole spacing
- 24 #12-24 mounting screws included
- Can be used with all Panduit cable management and patch panel products in addition to any industry standard 19" components
- Paint piercing washers included to electrically bond rack for simplified grounding. For the complete grounding solution, see the StructuredGround™ Kits for Racks
- 6" Rack, R2P6S is compatible with PatchRunner™ and High Capacity PatchRunner™ Products only

▪ Part Number	R2P79
▪ RoHS Compliancy Status	Compliant
▪ Part Description	19" EIA Rack, Aluminum 42RU Dimensions: 79.0"H x 20.2"W x 15.0"D (2004mm x 513mm x 381mm)
▪ Product Type	Rack
▪ Color	Black
▪ Depth (In.)	3.0
▪ Depth (mm)	76
▪ Height (In.)	79.0
▪ Height (mm)	2004
▪ Width (In.)	20.2
▪ Width (mm)	513
▪ No. of Rack Spaces	42
▪ Pricing Description	6.5 Foot Cable Management Rack
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.