Part Number : 1301030055
Product Description : Watertite Wet Location Incandescent Hand Lamp Only, 100W with Ungrounded Cast Aluminum Guard
Series Number : 130103
Status : Obsolete
Product Category : Lamps and Lights
Engineering Part Number : 1207



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Obsolete

Downloaded from Arrow.com.

Status	Obsolete
Category	Lamps and Lights
Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp Only, 100W with Ungrounded Cast Aluminum Guard
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps
UPC	78678861304

Agency

CSA	LR85374

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held

Obsolete

Downloaded from Arrow.com.

Outlet	None
Packaging Type	Carton

This document was generated on Sep 02, 2026

Obsolete

Downloaded from Arrow.com.