
**Part Number :** 5047541600
**Product Description :** Easy-On Back Flip FPC Connector with Lock Terminal, 0.30mm Pitch, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 16 Circuits
**Series Number :** 504754
**Status :** Active
**Product Category :** FFC / FPC Connectors



## Documents and Resources

### Drawings

5047541600_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

5047541600.dxf

### Specifications

5047549200-200.pdf

5047540000-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | FFC / FPC Connectors |
| Series | LA75 |
| Description | Easy-On Back Flip FPC Connector with Lock Terminal, 0.30mm Pitch, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 16 Circuits |
| Product Name | Easy-On |
| UPC | 889056610315 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 0.3A |
| Voltage - Maximum | 50V |

### Physical

| | |
|---|---|
| Actuator Type | Back Flip |
| Circuits (Loaded) | 16 |
| Color - Resin | Black |
| Contact Position | Dual |
| Durability (mating cycles max) | 10 |

Downloaded from Arrow.com.

| | |
|---|---|
| Mated Height | 0.75mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 22.413/mg |
| Orientation | Right Angle |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Mounting | Surface Mount |
| PCB Retention | No |
| Pitch - Mating Interface | 0.30mm |
| Pitch - Termination Interface | 0.30mm |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Wire/Cable Type | FPC only |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| 0.30mm Pitch Premo-Flex FPC Jumpers with Notches | 15031 |



Downloaded from Arrow.com.