

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/2/21	


APPROVED: _____

DATE: _____ TITLE: _____






CIRCUIT DIAGRAM
(SPST) OFF–MOM



PANEL CUTOUT
MAX. PANEL THICKNESS
4 mm



Seal Ring

SW–PB7–01PB4EBRXM

Button Color	
R	Red
G	Green
Y	Yellow
B	Blue
W	White
BK	Black

SPECIFICATIONS:
Material:
Bushing: Zinc Alloy, Nickel plated, color: Black
Base: PA
Contact: Silver alloy, (2.0x0.5mm)
Button: PBT
Electrical:
Switch Rating: 2A @ 36V DC
Contact resistance: 50 mΩ max initial.
Insulation resistance: 1000M ohms min.
Dielectric withstanding voltage: 1,500 VAC
Electrical Life: 200,000 cycles min.
Mechanical:
Operating Force: 3.5N
Nut Torque: 0.3Nm max.
Temperature Rating:
Operating temperature: –25°C to +55°C
Environmental:
IP65 Front Panel Protection
Lead free, RoHS compliant RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

DRAWN	WX	11/2/21
CHECKED	RC	11/2/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: SWITCH, ANTI-VANDAL, PUSH BUTTON, SPST, OFF-MOM, 12mm, RAISED COLOR BUTTON

SIZE	PART NO.	REV.
X	SW-PB7-01PB4EBRXM	-

REF: S00198T | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.