



NOTES:


1. ALL PARTS TO BE BULK PACKED.
2. CONTACTS ASSEMBLED INTO CONNECTOR.
3. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH A TOLERANCE.
4. DIMENSIONS IN BRACKETS [] ARE METRIC.
4. PC TAIL LENGTH OPTIONS:
 - STANDARD (SHORT) TAIL = 0.105in [W4281-1XSG-300]
 - INTERMEDIATE = 0.202in [W4291-1XSG-300]
 - LONG = 0.267in [W4292-1XSG-300]






MATING VIEW
W4292-10SG-300
10-POS.




MATING VIEW
W4292-11SG-300
11-POS.



MATING VIEW
W4292-12SG-300
12-POS.




STANDARD MULTI-CON-X



W4292-10SG-300 - 10-POS. (11&12 CLOSED)

W4292-11SG-300 - 11-POS. (12 CLOSED)

W4292-12SG-300 - 12-POS. (ALL OPEN)



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1
REV.	INIT.	DATE	DESCRIPTION
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF CONXALL CORPORATION. UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			
ORIG. DRAWN BY:	PAK	DATE: 10/22/14	
CHECKED BY:			
APPROVED BY:		TITLE: PANEL SOCKET, E-KEY	
SCALE: NTS	SIZE: B	SHEET: 1 OF 1	12-POS. #20 PC TAIL, LONG
REV. A			MULTI-CON-X, WEATHER RESISTANT
			CUSTOMER: STANDARD PRODUCT
►	= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX	FILE: W4292-1XSG-300	DIRECTORY: SLW
		PART NUMBER: W4292-1XSG-300	REV. A