

Han Pneumatic module, for 6mm contacts



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 002 4501
Specification	Han Pneumatic module, for 6mm contacts
HARTING eCatalogue	https://harting.com/09140024501

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Pneumatic module
Size of the module	Single module

Version

Gender	Male Female
Number of contacts	2
Details	Please order contacts separately. Using of guiding pins is imperative!

Technical characteristics

Limiting temperature	-40 ... +80 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	2
Net weight	8 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019973
eCl@ss	27440220 Module for industrial connectors (pneumatic)
ETIM	EC000438
UNSPSC 24.0	39121552