

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Mini
- Micro
- Accessory
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



MC-05PMMS-SH8001

Operating Temperature: -20°C ~ +80°C
Transmission Speed: N/A
Shielded: Metal, Non-shielded
Jacket Material: PVC
Certificate: N/A

You must login first for view the price


Quantity - 1 +

Can't find? [Customize your part](#)

Mating Pair & Accessories


Connector Type ▼ Search



M Series....
CAP-WBDMQPC1
-20°C ~ +80°C

- 0 +


☐



M Series....
CAP-WBDMMSMA2
-40°C ~ +105°C

- 0 +


☐



NMEA 2000....
E-555500-...
-20°C ~ +85°C

- 0 +


☐



NMEA 2000....
E-555500-...
-20°C ~ +85°C

- 0 +


☐



NMEA 2000....
E-555500-...
-20°C ~ +85°C

- 0 +


☐



NMEA 2000....
E-555500-...
-20°C ~ +85°C

- 0 +

☐

Specifications	Download / CAD
Nominal Current 4A	Connector Type Receptacle With Wires
Shielded Metal, Non-shielded	No. of Contacts 05
Connector Gender Male	Backshell Hexagonal
Mating Style Screw Thread	IP Rating IP68
Assembly Style Solder	
➕ More Options	

People Also Bought

