


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	ECR-16-010326	07JUL2016	DW	CW
	A4	ECR-16-018349	30DEC2016	DW	CW
	B	ECR-20-008190	05AUG2020	WQR	CW
	B1	ECR-21-105138	25JUN2021	WQR	CW




SCALE 1:2





NOTES:
1. TECHNICAL CHARACTERISTICS:
   HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
   HOOD SURFACE: POWDER COATED, GREY, RAL7037
   DEGREE OF PROTECTION: IP65 (MATED)

注释：
1. 技术参数：
   上壳材料： 铝合金
   上壳表面处理： 灰色粉末涂层，RAL7037
   防护等级： IP65(配合)



PART NUMBER 零件料号		PART DESCRIPTION 零件描述	PG/M THREAD PG/M 螺纹孔
T1230160121-000	H16B-TSH-PG21	H16B HOOD,SIDE ENTRY PG21,4 EAR,HIGH CONSTRUCTION,POWDER COATED,GREY H16B上壳，侧出PG21，4耳，高结构，灰色粉末喷涂	PG21
T1230160129-000	H16B-TSH-PG29	H16B HOOD,SIDE ENTRY PG29,4 EAR,HIGH CONSTRUCTION,POWDER COATED,GREY H16B上壳，侧出PG29，4耳，高结构，灰色粉末喷涂	PG29
T1230160125-000	H16B-TSH-M25	H16B HOOD,SIDE ENTRY M25,4 EAR,HIGH CONSTRUCTION,POWDER COATED,GREY H16B上壳，侧出M25，4耳，高结构，灰色粉末喷涂	M25
T1230160132-000	H16B-TSH-M32	H16B HOOD,SIDE ENTRY M32,4 EAR,HIGH CONSTRUCTION,POWDER COATED,GREY H16B上壳，侧出M32，4耳，高结构，灰色粉末喷涂	M32
T1230160140-000	H16B-TSH-M40	H16B HOOD,SIDE ENTRY M40,4 EAR,HIGH CONSTRUCTION,POWDER COATED,GREY H16B上壳，侧出M40，4耳，高结构，灰色粉末喷涂	M40

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
-

FINISH -
-

DWN DAVID WANG 11JUN2014
CHK CHRIS WANG 11JUN2014
APVD XIANG XU 11JUN2014
PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013
WEIGHT -

TE Connectivity

NAME H16B-TSH-M/PG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-T1230160 1XX000	

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV B1

1471-9 (3/13)

Downloaded from Arrow.com.