



**Part Number :** [1301120160](#)  
**Product Description :** Construction Snap-on Bottom  
Cover  
**Series Number :** 130112  
**Status :** Active  
**Product Category :** Portable Lighting Accessories  
**Engineering Part Number :** 370



Documents and Resources

Product Environment Compliance

Compliance

|                    |                                               |
|--------------------|-----------------------------------------------|
| GADSL/IMDS         | Not Relevant                                  |
| China RoHS         | Not Reviewed per SJ/T 11365-2006              |
| EU ELV             | Not Relevant                                  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21               |
| REACH SVHC         | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS            | Not Reviewed per EU 2015/863                  |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

## Part Details

### General

|                    |                                   |
|--------------------|-----------------------------------|
| Status             | Active                            |
| Category           | Portable Lighting Accessories     |
| Series             | 130112                            |
| Description        | Construction Snap-on Bottom Cover |
| NEMA Configuration | N/A                               |
| Product Name       | Woodhead                          |
| Type               | Accessory                         |
| UPC                | 78678861170                       |

### Electrical

|                             |     |
|-----------------------------|-----|
| Lamp Wattage - Maximum      | N/A |
| Lumens                      | N/A |
| On/Off Switch               | N/A |
| Voltage (Fixture) - Maximum | N/A |

### Physical

|                         |                            |
|-------------------------|----------------------------|
| Bulb Type               | N/A                        |
| Cord Length - Primary   | N/A                        |
| Cord Length - Secondary | N/A                        |
| Depth                   | 120.65mm (4.750")          |
| Duty                    | Commercial                 |
| Guard Included          | No                         |
| Guard Type              | N/A                        |
| Height                  | 14.22mm (.560")            |
| Lamp Type               | A21                        |
| Length                  | N/A                        |
| Material - Guard        | #8 Gauge Zinc-plated Steel |
| Net Weight              | 22.679/g                   |
| Outlet                  | None                       |
| Packaging Type          | Carton                     |

---

This document was generated on May 27, 2026