# Datasheet for part number HDX-WC1M0-09XMB

| |
|---|
| Our Catalog Part Number: HDX-WC1M0-09XMB |
| Our Global Manufacturing Part Number: 155910-0002 |
| Brand: Cannon Product Category: HDx Product Line: HDx Series: HDX |

| Product Datasheet | |
|---|---|
| Series | HDXW High Density Series |
| Connector Type | Plug, In Line |
| Coupling Style | Locking Nut |
| Shell Style | In Line |
| Shell Material | Brass Alloy |
| Plating | Ruthenium over Electroless Nickel |
| Contact Arrangement | 0-09 |
| Contact Quantity | 9 |
| Contact Type | Solder Cup |
| Contact Gender | Pin |
| Contact Size | Combo/Mixed 3 x 0.3mm + 6 x 0.7mm |
| Polarization | Red Color Code |
| Receptacle Earth Tag | No |
| Wire Accommodation | 3 x 28 AWG + 6 x 22 AWG |
| Currrent Rating | 3 x 1A + 6 x 5A |
| Operating Voltage | 250VDC |
| Operating Temperature | -51°C to +125°C |
| Durability | 5,000 mating cycles |
| Salt Spray | 96 Hrs Salt Fog |
| Water Immersion | 20 meters for 120 mins |

Specifications and dimensions subject to change.



Downloaded from Arrow.com.