Part Number : 1300100119
Product Description : Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), 16 AWG, Yellow TPE Cable, 2.0m (6.56') Length
Series Number : 130010
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 115033K13M020



Documents and Resources

Drawings

1300100119_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Phosphine oxide, diphenyl(2,4,6-trimethylbenzoyl) per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130010
Description	Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), 16 AWG, Yellow TPE Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Double Ended
UPC	78678808132

Agency

UL	E152210

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

Physical

Cable Diameter	12.70mm (.500")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded

Downloaded from Arrow.com.

Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	410.875/g
Orientation	90° to 90°
Poles	5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	TPE
Wire Size (AWG)	16

Downloaded from Arrow.com.