

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing



1412826

<https://www.phoenixcontact.com/us/products/1412826>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Box mounting bases B6, with single locking latch, material: Die-cast aluminum, salt water resistant, protective cover material: PC, cable outlets: 2, lateral, 2x M25, height: 54.6 mm, cable gland: none, protective cover: yes, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1412826
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 599 (C-2-2019)
GTIN	4055626060835
Weight per piece (including packing)	209.8 g
Weight per piece (excluding packing)	204.4 g
Customs tariff number	85389099
Country of origin	PL

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing



1412826

<https://www.phoenixcontact.com/us/products/1412826>

Technical data


Notes

General	For contact inserts HC-B6, BB10, DD24, M Tall housings for extra large wiring space
General	also available as a powder-coated or color version: 1372610 HC-STA-B06-SLWSC-2SSM25-EL/.../...

Product properties

Product type	Housing with locking latch
Housing type	Box mounting bases
Application	Standard
Type	B6
No. of cable outlets	2
Type of the screw connection	2x M25
Type	Low design
Protective cover	yes
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	52 mm
Height	54.6 mm
Length	84 mm
Hole diameter	5.5 mm

Material specifications

Flammability rating according to UL 94	V0 (Interlock) V0 (Protective cover)
Seal material	NBR, conductive
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated
Material, protective cover	PC
Locking latch material	PA

Mechanical properties

Mechanical data

Type of the screw connection	2x M25
Locking type	Latch

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing



1412826

<https://www.phoenixcontact.com/us/products/1412826>

Connection data

Tightening torque	2 Nm ... 3 Nm (for M5 mounting screws on the surface-mount housing)
-------------------	---

Mounting

Assembly note	One opening is sealed with a plastic filler plug and can be opened using a screwdriver.
---------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66 (with locked protective cover)
	IP67 (when plugged in)
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing




1412826

<https://www.phoenixcontact.com/us/products/1412826>

Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing



1412826

<https://www.phoenixcontact.com/us/products/1412826>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412826>

DNV
Approval ID: TAE000037S

EAC
Approval ID: RU C-DE.AI30.B.01102

EAC
Approval ID: RU C-DE.BL08.B.00511

cUL Recognized
Approval ID: E255026

UL Recognized
Approval ID: E255026

cULus Recognized

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing



1412826

<https://www.phoenixcontact.com/us/products/1412826>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing



1412826

<https://www.phoenixcontact.com/us/products/1412826>

Accessories

G-INS-M25-M68N-NNES-S - Cable gland

1411165

<https://www.phoenixcontact.com/us/products/1411165>



Cable gland, material for screw connection: Brass, nickel-plated, application: Standard, external cable diameter 11 mm ... 17 mm, shielding: no, connecting thread: M25 x 1.5, color: silver, with O-ring

G-INSEC-M25-S68N-NCRS-S - Cable gland

1411190

<https://www.phoenixcontact.com/us/products/1411190>



Cable gland, material for screw connection: Brass, nickel-plated, application: EMC, external cable diameter 11 mm ... 16 mm, shielding: yes, connecting thread: M25 x 1.5, color: silver, with O-ring

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing

1412826

<https://www.phoenixcontact.com/us/products/1412826>



HC-M-KV-M25(1ASI) - Cable gland

1584020

<https://www.phoenixcontact.com/us/products/1584020>



Metal screw connection for an AS-Interface flat-ribbon conductor, thread type M25

HC-STA-B06-SL-PLBK - Housing brackets

1412591

<https://www.phoenixcontact.com/us/products/1412591>



Single locking latch for B6 housing, HC-EVO....AL and HC-STA....AL

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing

1412826

<https://www.phoenixcontact.com/us/products/1412826>



HC-B06-SP-CBK - Profile gasket

1411477

<https://www.phoenixcontact.com/us/products/1411477>

Profile gasket for HEAVYCON EVO supporting base element type B6, conductive



HC-B06-BC-HI-PLBK - Protective cover

1407692

<https://www.phoenixcontact.com/us/products/1407692>

Protective cover B6, for single locking latch, protective cover material: PC, height: 19 mm, seal: no



HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing

1412826

<https://www.phoenixcontact.com/us/products/1412826>



HC-STA-B06-DC-PL - Protective cover

1421100

<https://www.phoenixcontact.com/us/products/1421100>

Protective cover, design: B6



WP-G HF IP66 M25 BK - Screw connection

3240899

<https://www.phoenixcontact.com/us/products/3240899>

Cable gland, metric thread, IP66 protection, straight



HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing

1412826

<https://www.phoenixcontact.com/us/products/1412826>



WP-G HF IP69K M25 BK - Screw connection

3240885

<https://www.phoenixcontact.com/us/products/3240885>

Cable gland, metric thread, IP68/69k protection, straight



WP-GA HF IP66 M25 BK - Screw connection

3240927

<https://www.phoenixcontact.com/us/products/3240927>

Cable gland, metric thread, IP66 protection, angled



HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing

1412826

<https://www.phoenixcontact.com/us/products/1412826>



WP-GA HF IP69K M25 BK - Screw connection

3240913

<https://www.phoenixcontact.com/us/products/3240913>

Cable gland, metric thread, IP68/69k protection, angled



WP-GR HF IP66 M25 BK - Screw connection

3240955

<https://www.phoenixcontact.com/us/products/3240955>

Cable gland, metric thread, IP66 protection, with strain relief



HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing

1412826

<https://www.phoenixcontact.com/us/products/1412826>



WP-GR HF IP69K M25 BK - Screw connection

3240941

<https://www.phoenixcontact.com/us/products/3240941>



Cable gland, metric thread, IP68/69k protection, with strain relief

WP-G PP HF M25 - Screw connection

3240999

<https://www.phoenixcontact.com/us/products/3240999>



Cable gland made from PP with metric thread, IP65 protection

HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing



1412826

<https://www.phoenixcontact.com/us/products/1412826>

WP-GT PP HF M25 - Screw connection

3241013

<https://www.phoenixcontact.com/us/products/3241013>

Cable gland made from PP with metric thread, rotatable, IP54 protection



WP-G BRASS IP40 M25 - Screw connection

3241048

<https://www.phoenixcontact.com/us/products/3241048>

Cable gland made from brass with metric thread, IP40 protection



HC-STA-B06-SLWSC-2SSM25-ELC-AL - Housing



1412826

<https://www.phoenixcontact.com/us/products/1412826>

WP-GT BRASS M25 - Screw connection

3241034

<https://www.phoenixcontact.com/us/products/3241034>

Cable gland made from brass with metric thread, rotatable, IP40 protection



WP-G BRASS IP65 M25 - Screw connection

3241062

<https://www.phoenixcontact.com/us/products/3241062>

Cable gland made from brass with metric thread, IP65 protection



Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com