


YAV14H, Uninsulated Ring Terminal For 16 - 14 AWG

By Burndy

Catalog # [YAV14H](#)



Copper Compression Lug, Heavy Duty, Ring Tongue with Shroud, 1 Hole w/ Inspection Hole, 20-14 AWG, #8-#10 Stud, Short Barrel, Tin Plated.

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors

General

Catalog Number	YAV14H
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810024959
UPC 14 Digit GTIN	00781810024959

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.247 in
Dimension - Bolt Size fraction	#10
Dimension - D inch	0.42 in
Dimension - Length Overall inch	0.95 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.24 in
Dimension - Pad Width inch	0.31 in
Dimension - Stud Size inch	#10
Dimension - Z (inch)	0.24 in

Conductor Related

Conductor - Copper Str Size Range	20 AWG;18 AWG;16 AWG;14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> CU C Solid-Size CU C Str-Size

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_YAV14H_LineArt](#)

[Sales Drawings - 50094162](#)

[Specifications - YAV14H](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YAV14H-SPEC-EN | REV 7/2025