

M17 Crimp Contact 1,0mm,male,0,08-0,14mm



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 065 0000
Specification	M17 Crimp Contact 1,0mm,male,0,08-0,14mm
HARTING eCatalogue	https://harting.com/21170650000

Identification

Category	Contacts
Series	Circular connectors M17
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.08 ... 0.14 mm ²
Conductor cross-section [AWG]	AWG 28 ... AWG 26
Stripping length	5 mm
Limiting temperature	-40 ... +125 °C

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances Not contained

Commercial data

Packaging size	100
Net weight	0.3 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140819795
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522
