

Part Number : [386608810](#)


Product Description : 12.70mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, 600V, 10 Circuits

Series Number : 38660

Status : Obsolete

Product Category : Terminal Blocks and Barrier Strip

Engineering Part Number : 66510-RC



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Terminal Blocks and Barrier Strip
Series	38660
Description	12.70mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, 600V, 10 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Fixed Mount Barrier
Type	Barrier Strips
UPC	883906403126

Electrical

Current - Maximum per Contact	45.0A
Voltage - Maximum	600V

Physical

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polysulfone
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PCB Retention	Yes
PC Tail Length	4.06mm

Pitch - Mating Interface	N/A
Pitch - Termination Interface	12.70mm
Polarized to Mating Part	N/A
Shrouded	Tri-Barrier
Stackable	No
Temperature Range - Operating	-40° to +110°C
Wire Size (AWG)	10, 12, 14, 16, 18, 8
Wire Size mm ²	0.82-8.37

This document was generated on Dec 31, 2025

Obsolete