

Search within category

GO

PFM0040



FLR Sign, NONSKD, 6X24, RED WHITE STRPES
Sold in US and Canada only

BUY NOW

DESIGN / INSTALL

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Color	Red/White			
Material	PVC/Aluminum Oxide			
Overall Width (In.)	24			
Overall Width (mm)	609.6			
Maximum Operating Temperature (°C)	60			
Maximum Operating Temperature (°F)	140			
Note	Sold in US and Canada only			
Minimum Operating Temperature (°C)	-28			
Minimum Operating Temperature (°F)	-20			
Application	Mark floor messages with a high-traction surface.			
Dimensions (In.)	6" x 24"			
Environment	2 years			
Legend	(DIAGONAL STRIPE PATTERN)			
Operating Temperature	-20°F to 140°F			
Overall Height (In.)	6.00			
Overall Height (mm)	152.4			
Part Features	Constructed of 20-mil self-adhesive vinyl, Sub-surface printed bold graphics and messages are overlaminated with a protective layer, Durable, non-slip, rough surface helps maintain safe stepping on wet or greasy floors, Permanent acrylic adhesive back with peel-off liner.			
UL Listed	No			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			