



Part Number : [2290961222](#)

Product Description : Pre-Crimped Lead Zero-Hachi Female-to-Zero-Hachi Female, 0.10µm Gold (Au) Plating, 150.00mm Length, 28 AWG, Black

Series Number : 229096

Status : Active

Product Category : Power and Signal Cable Assemblies




Documents and Resources

Drawings

[2290961222 sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)6375-DC (05 Nov 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|------------------------|-------------------------------------------------------------------------------------------------------------------|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 229096 |
| Description | Pre-Crimped Lead Zero-Hachi Female-to-Zero-Hachi Female, 0.10µm Gold (Au) Plating, 150.00mm Length, 28 AWG, Black |
| Application | Signal, Wire-to-Board |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | Zero-Hachi Terminal-to-Zero-Hachi Terminal |
| Keyword | Pre-Crimped Leads |
| Product Name | Zero-Hachi |
| UPC | 198930256205 |

Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 30V AC (RMS)/DC |

Physical

| | |
|--------------------------------|---------------|
| Cable Length | 150.00mm |
| Circuits (Loaded) | 1 |
| Circuits (maximum) | 1 |
| Color - Resin | Black |
| Gender | Female-Female |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Net Weight | 0.193/g |

| | |
|-----------------------------|----------------------|
| Packaging Type | Bag |
| Plating min - Mating | 0.100µm |
| Plating min - Termination | 0.050µm |
| Single Ended | No |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | UL 10064 |
| Wire Size (AWG) | 28 |

Mates With / Use With

Use with Part(s)

| Description | Part Number |
|-------------------------------------------|---------------|
| Zero-Hachi Single Row Receptacle Housings | <u>214719</u> |

This document was generated on Feb 01, 2026