

**FTL-PPE002M | 1358548****TracerLight® Fiber Optic Patch Cord, 1.7 mm duplex, multimode, LC/UPC to LC/UPC, orange 2 m**

- Offers a quick and accurate method of identifying the termination point of optical patch cords
- Each end of a TracerLight patch cord features a flashing light source allowing technicians to visually trace individual patch cords
- Dramatically minimizes the risk of taking the wrong fiber out of service while improves system turn-up speed and accuracy
- Ideally suited for Central Offices, Data Centers and cross-connect patching

## Product Classification

Brand	TracerLight®
Product Series	FTL
Product Type	Fiber patch cord, duplex
Regional Availability	Latin America   North America

## Body Features

Connector Color (End A)	Beige
Connector Color (End B)	Beige

## Configuration Features

Number of Connectors (End A)	2
Number of Connectors (End B)	2

## Construction Materials

Jacket Color	Orange
Total Fibers, quantity	2

## Dimensions

Assembly Length	2.00 m   6.56 ft
-----------------	------------------

## General Specifications

Interface, connector A	LC
Interface, connector B	LC
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard

## Product Type Features

Fiber Type	OM2
Fiber Diameter	50/125 µm
Optical Mode	Multimode

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

## \* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---