

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
MINNEAPOLIS, MINNESOTA

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-3RW822T

AQF6500

M BZ-3RW822T
PAGE 1 OF 1

DRAWING
NUMBER

ISSUE
12

REPLACES

RELEASE NO.

CHECK

29 AUG 05

RJ

CHECK

11 APR 92

H


CHECK

9 APRIL 62

GCH

REVISIONS

A	CO	16736
8	CH	9 APRIL 62
B	CO	034306
15	D J W	15 JUL 73
C	CO	59351-D
18	JWB	18 JUL 91
D	CO	7018 4-G
14	G J W	14 MAR 92
E	CO	75204-B
11	W L S	11 FEB 94
F	CO	77589
29	TSM	29 MAR 94
G	CO	093346
18	DLT	18 SEP 98
H		203837
	TSM	30 AUG 01
J		0015138
	SPK	29 AUG 05



NOTE

△ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 6 1/2 OZ MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 1 1/2 OZ MIN		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL ----- .007 - .030		TOLERANCES ARE:
OVERTRAVEL ----- .094 MIN		ONE PLACE (.0) ± .030
		TWO PLACE (.00) ± .015
		THREE PLACE (.000) ± .008
		ANGLES ±
		WEIGHT .076 LB

-L96- 15A-125, 250, OR 480 VAC
1/2 A-125 VDC; 1/4 A-250 VDC
1/8 HP-125 VAC; 1/4 HP-250 VAC

-L288-
-L306-
-L315-

CE EN05 EC T85 5E4

RASTOR

FO-50378

DRAWN