

Han CGM-P M40x1,5 D.20-26mm black



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 00 000 5188 |
| Specification | Han CGM-P M40x1,5 D.20-26mm black |
| HARTING eCatalogue | https://harting.com/19000005188 |

Identification

| | |
|--------------------------|------------------------|
| Category | Accessories |
| Series of hoods/housings | Han [®] CGM-P |
| Type of accessory | Cable gland |

Technical characteristics

| | |
|--|--|
| Tightening torque | ≤10 Nm (depending on the cable and the seal insert used) |
| Wrench size | 53 |
| Limiting temperature | -40 ... +100 °C |
| Degree of protection acc. to IEC 60529 | IP68 IP69 / IPX9K acc. to ISO 20653 |
| Size | M40 |
| Clamping range | 20 ... 26 mm |
| Width across corners | 58.8 mm |

Material properties

| | |
|---|----------------------|
| Material (cable glands) | Polyamide (PA) |
| Colour (cable gland) | RAL 9005 (jet black) |
| Material (seal) | NBR |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Specifications and approvals

| | |
|-----------|----------------------------------|
| UL / CSA | UL 514B QCRV.E479780 |
| | CSA-C22.2 No. 18.3 QCRV7.E479780 |
| Approvals | DNV GL |

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 1 |
| Net weight | 74 g |
| Country of origin | Germany |
| European customs tariff number | 39269097 |
| GTIN | 5713140192935 |
| eCl@ss | 27140801 Screwed cable gland (electrical) |
| ETIM | EC000441 |
| UNSPSC 24.0 | 39121431 |